



1 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

By Raco
Catalog # 1224



*Representative Image

1 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012246

Dimensions

Dimensions	0.969 in x 1.75 in x 2.25 in
Height	2.25 in
Length	0.969 in
Trade Size	1 in
Weight	0.121 lb
Width	1.75 in

Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Certified Listed	UL Listed CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	50
Pallet Quantity	16000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-1](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1224-SPEC-EN | REV 6/2024