



1-1/4 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

By Raco
Catalog # 1225



*Representative Image

1-1/4 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012253

Dimensions

Dimensions	1.281 in x 2.125 in x 2.625 in
Height	2.625 in
Length	1.281 in
Trade Size	1-1/4 in
Weight	0.2 lb
Width	2.125 in

Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Certified Listed	UL Listed
	CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	12375

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC-E195975-1](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1225-SPEC-EN | REV 6/2024