



# 3-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through- Lug, Insulated

By Raco  
Catalog # 1234

3-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Feed-Through-Lug, Insulated

## Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #6 Str. - #250 MCM
- UL and CSA Listed
- Available in trade sizes of 1/2 in. through 4 in.

## General

Catalog Number	1234
Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012345

## Dimensions

Dimensions	3.375 in x 4.406 in x 5.25 in
Height	5.25 in
Length	3.375 in
Trade Size	3-1/2 in
Weight	0.824 lb
Width	4.406 in



\*Representative Image

## Electrical Ratings

Grounding Wire Capacity Maximum	#250 MCM
Grounding Wire Capacity Minimum	#6 STR

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1890

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC-E195975-1](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Specifications - 1234](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand