



2-1/2 in. Rigid/IMC Bonding Locknut

By Raco
Catalog # 1250

2-1/2 in. Rigid/IMC Bonding Locknut

Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 4 in.

General

Catalog Number	1250
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Locknuts
Material	Steel
UPC	050169012505

Dimensions

Dimensions	0.45 in x 3.31 in x 3.52 in
Height	3.52 in
Length	0.45 in
Trade Size	2-1/2 in
Weight	0.2 lb



*Representative Image

Width	3.31 in
-------	---------

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	5600

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195975- 1](#)
- [Certifications - UL COC-E195975-2](#)
- [Product Logo - Conduit](#)
- [SDS - HCC SDS](#)
- [Specifications - 1250](#)
- [Terms and Conditions - HCC Terms & Conditions](#)