



## 3 in. Rigid/IMC Bonding Locknut

By Raco  
Catalog # [1252](#)

3 in. Rigid/IMC Bonding Locknut



\*Representative Image

### Features

- All steel construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- UL and CSA Listed
- Available in trade sizes 1/2 in. through 4 in.

### General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Locknuts
Item Type	4D
Material	Steel
UPC	050169012529

### Dimensions

Dimensions	0.45 in x 4 in x 4.19 in
Height	4.19 in
Length	0.45 in
Trade Size	3 in
Weight	0.237 lb
Width	4 in

### Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3360

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195975- 1](#)  
[Certifications - UL COC-E195975-2](#)  
[Product Logo - Conduit](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-1252-SPEC-EN | REV 6/2024