



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 & Six 3/4 in. KO's, Raised Ground

By Raco
Catalog # 126



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 & Six 3/4 in. KO's, Raised Ground

Features

- Drawn steel construction with raised ground screw area
- 4 in. x 1-1/2 in. deep
- Supplied with two 1/2 in. and six 3/4 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

General

Bracket Type	No Bracket
Catalog Number	126
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in;3/4 in
Material	Steel
Number of Gang(s)	1-Gang
Size	4 in
Type	Box
UPC	050169001264
Wiring System	Conduit

Dimensions

Actual Depth	1.563 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	4 in
Raised Ground	Yes
Weight	0.504 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	3500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-126-SPEC-EN | REV 6/2024