



# 1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco  
Catalog # 1262DC



\*Representative Image

1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug,  
Insulated

## Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #4 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

## General

Conduit Type	Rigid/IMC
Connector Type	Grounding
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169916285

## Dimensions

Dimensions	0.578 in x 1.156 in x 1.531 in
Height	1.531 in
Length	0.578 in
Trade Size	1/2 in
Weight	0.078 lb
Width	1.156 in

## Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

## Certifications And Compliance

Certified Listed	UL Listed CSA Certified
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	25200

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-1262DC-SPEC-EN | REV 6/2024