



## 3/4 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco  
Catalog # 1263DC

3/4 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated



\*Representative Image

### Features

- Lay-in and Fee-thru lug styles provide an easy means of inserting a ground wire
- Dual rated aluminum grounding lugs may be used with copper or aluminum grounding conductors
- Insuliner temperature rated at 150° C
- Malleable iron construction insures mechanical protection for the raceway
- Zinc electroplated for corrosion protection
- Additional sizes available

### General

Conduit Type	Rigid/IMC
Connector Type	Grounding
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169916292

### Dimensions

Dimensions	0.75 in x 1.406 in x 1.781 in
Height	1.781 in
Length	0.75 in
Trade Size	3/4 in
Weight	0.114 lb
Width	1.406 in

### Electrical Ratings

Grounding Wire Capacity Maximum	#4 STR
Grounding Wire Capacity Minimum	#14 SOL

### Certifications And Compliance

Certified Listed	UL Listed CSA Certified
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	14000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-1263DC-SPEC-EN | REV 6/2024