



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 & Four 3/4 in. KO's, Raised Ground, TS Bracket

By Raco
Catalog # 127TS

4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 & Four 3/4 in. KO's, Raised Ground, TS Bracket



Features

- Welded steel construction with raised ground screw area and "TS" side-mount bracket with gauging tabs and recessed nailing spurs
- 4 in. x 1-1/2 in. deep
- Supplied with three 1/2 in. and four 3/4 in. knockouts
- Combination screw heads provide for faster installation
- 15.5 cu. in. capacity

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Ceiling Fan Rated	No
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in.; 3/4 in
Material	Steel
Size	4 in
Type	Box
UPC	050169501276
Wiring System	Conduit

Dimensions

Actual Depth	1.813 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	7 in
Raised Ground	Yes
Weight	0.628 lb
Width	3.938 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Pallet Quantity	2250

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978- 2](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Sell Sheets - 4 in. Octagon Box with 3/4 in. KO and TS Bracket](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-127TS-SPEC-EN | REV 6/2024