



2-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

By Raco
Catalog # 1290

2-1/2 in. 150 Degree Rigid/IMC Grounding Bushing, Lay-in-Lug, Insulated

Features

- Malleable iron construction ensures mechanical protection
- Zinc-electroplated for added corrosion protection
- Insuliner rated for 150° C
- Grounding Wire Capacity - #14 Sol. - #1/0 Str.
- UL and CSA Listed
- Available in trade sizes of 1/2 in through 4 in.

General

Catalog Number	1290
Conduit Type	Rigid/IMC
Connector Type	Grounding
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Malleable Iron
UPC	050169012901

Dimensions

Dimensions	2.297 in x 3.281 in x 3.875 in
Height	3.875 in
Length	2.297 in
Trade Size	2-1/2 in
Weight	0.364 lb
Width	3.281 in



*Representative Image

Electrical Ratings

Grounding Wire Capacity Maximum	#1/0 STR
Grounding Wire Capacity Minimum	#14 SOL

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2940

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC-E195975-1](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Specifications - 1290](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand