



3/4 in. EMT or 1/2 in. Rigid/IMC Clamp Back

By Raco
Catalog # 1342

3/4 in. EMT or 1/2 in. Rigid/IMC Clamp Back

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1342
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013427

Dimensions

Dimensions	2.297 in x 1.031 in x 0.422 in
EMT Size	0.75 in
Height	0.422 in
Length	2.297 in



*Representative Image

Rigid/IMC Size	0.5 in
Trade Size	Rigid/IMC 1/2 in, EMT 3/4 in
Weight	0.071 lb
Width	1.031 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	32000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Product Logo - Conduit](#)
[Sales Drawings - 1342 Customer Drawing](#)
[SDS - HCC SDS](#)
[Specifications - 1342](#)
[Terms and Conditions - HCC Terms & Conditions](#)