



1-1/4 in. EMT or 1 in. Rigid/IMC Clamp Back

By Raco
Catalog # 1344

1-1/4 in. EMT or 1 in. Rigid/IMC Clamp Back



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1344
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013441

Dimensions

Dimensions	3.016 in x 1.266 in x 0.531 in
EMT Size	1.25 in
Height	0.531 in
Length	3.016 in
Rigid/IMC Size	1 in
Trade Size	Rigid/IMC 1 in, EMT 1-1/4 in
Weight	0.155 lb
Width	1.266 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Pallet Quantity	16000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[Sales Drawings - 1344 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand