



## 2 in. EMT or 1-1/2 in. Rigid/IMC Clamp Back

By Raco  
Catalog # 1346

2 in. EMT or 1-1/2 in. Rigid/IMC Clamp Back

### Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

### General

|                          |                      |
|--------------------------|----------------------|
| Catalog Number           | 1346                 |
| Conduit Type             | Rigid/IMC            |
| EU RoHS Indicator        | Contact Manufacturer |
| Environmental Conditions | Wet Location         |
| Fitting Type             | Straps/Clampbacks    |
| Material                 | Malleable Iron       |
| UPC                      | 050169013465         |

### Dimensions

|            |                              |
|------------|------------------------------|
| Dimensions | 3.906 in x 1.609 in x 0.5 in |
| EMT Size   | 2 in                         |
| Height     | 0.5 in                       |
| Length     | 3.906 in                     |



\*Representative Image

|                |                              |
|----------------|------------------------------|
| Rigid/IMC Size | 1.5 in                       |
| Trade Size     | Rigid/IMC 1-1/2 in, EMT 2 in |
| Weight         | 0.245 lb                     |
| Width          | 1.609 in                     |

### Certifications And Compliance

|                          |                      |
|--------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
| Certified Listed         | UL Listed            |

### Logistics

|                       |      |
|-----------------------|------|
| Carton Quantity       | 25   |
| Minimum Pack Quantity | 25   |
| Pallet Quantity       | 8000 |

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - 1346 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Specifications - 1346](#)  
[Terms and Conditions - HCC Terms & Conditions](#)