



2-1/2 in. EMT or Rigid/IMC Clamp Back

By Raco
Catalog # 1347

2-1/2 in. EMT or Rigid/IMC Clamp Back



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013472

Dimensions

Dimensions	2.75 in x 2.406 in x 0.828 in
EMT Size	2.5 in
Height	0.828 in
Length	2.75 in
Rigid/IMC Size	2.5 in
Trade Size	2-1/2 in
Weight	0.8 lb
Width	2.406 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	4900

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand