



2 in. EMT or Rigid/IMC Clamp Back

By Raco
Catalog # 1348

2 in. EMT or Rigid/IMC Clamp Back



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1348
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013489

Dimensions

Dimensions	4.844 in x 1.984 in x 0.922 in
EMT Size	2 in
Height	0.922 in
Length	4.844 in

Rigid/IMC Size	2 in
Trade Size	2 in
Weight	0.556 lb
Width	1.984 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	3200

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 1348 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 1348](#)
- [Terms and Conditions - HCC Terms & Conditions](#)