



3 in. EMT or Rigid/IMC Clamp Back

By Raco
Catalog # 1349

3 in. EMT or Rigid/IMC Clamp Back



*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1349
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013496

Dimensions

Dimensions	6.734 in x 2.625 in x 0.844 in
EMT Size	3 in
Height	0.844 in
Length	6.734 in
Rigid/IMC Size	3 in
Trade Size	3 in
Weight	0.953 lb
Width	2.625 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1349-SPEC-EN | REV 6/2024