



3-1/2 in. EMT or Rigid/IMC Clamp Back

By Raco
Catalog # 1350



3-1/2 in. EMT or Rigid/IMC Clamp Back

*Representative Image

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013502

Dimensions

Dimensions	7.656 in x 3.266 in x 0.953 in
EMT Size	3.5 in
Height	0.953 in
Length	7.656 in
Rigid/IMC Size	3.5 in
Trade Size	3-1/2 in
Weight	1.41 lb
Width	3.266 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand