



4 in. EMT or Rigid/IMC Clamp Back

By Raco
Catalog # 1351



4 in. EMT or Rigid/IMC Clamp Back

Features

- Malleable iron construction ensures mechanical protection
- Elongated bolt holes allows easy alignment with the conduit strap
- UL Listed
- Available in trade sizes of 1/2 in. through 4 in.

General

Catalog Number	1351
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Wet Location
Fitting Type	Straps/Clampbacks
Material	Malleable Iron
UPC	050169013519

Dimensions

Dimensions	8.078 in x 3.438 in x 1.031 in
EMT Size	4 in
Height	1.031 in
Length	8.078 in
Rigid/IMC Size	4 in
Trade Size	4 in
Weight	1.696 lb
Width	3.438 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1200

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[Sales Drawings - 1351 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand