



3/4 in. EMT or Rigid/IMC Compression Threaded Coupling

By Raco
Catalog # 1353



*Representative Image

3/4 in. EMT or Rigid/IMC Compression Threaded Coupling

Features

- All steel construction ensures mechanical protection
- All components are zinc electroplated for corrosion protection
- UPC bar code fittings are individually polybagged with a preprinted UPC-A bar code and packaged in pre-scored tear top cartons for an attractive presentation
- Additional sizes available

General

Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Couplings
Material	Steel
UPC	050169013533

Dimensions

Dimensions	1.532 in x 1.375 in x 1.375 in
Height	1.375 in
Length	1.532 in
Trade Size	3/4 in
Weight	0.164 lb
Width	1.375 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	10125

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1353-SPEC-EN | REV 6/2024