



3/4 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1403



*Representative Image

3/4 in. Rigid/IMC Bushing, Insulated

Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

General

Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Polypropylene
UPC	050169014035

Dimensions

Dimensions	0.407 in x 1.29 in x 1.29 in
Height	1.29 in
Length	0.407 in
Trade Size	3/4 in
Weight	0.009 lb
Width	1.29 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	400
Minimum Pack Quantity	100
Pallet Quantity	38400

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195973-1](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1403-SPEC-EN | REV 6/2024