



1-1/4 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1405



*Representative Image

1-1/4 in. Rigid/IMC Bushing, Insulated

Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

General

| | |
|-------------------|----------------------|
| Conduit Type | Rigid/IMC |
| EU RoHS Indicator | Contact Manufacturer |
| Fitting Type | Bushings |
| Insulation Type | Insulated |
| Material | Polypropylene |
| UPC | 050169014059 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 0.485 in x 1.953 in x 1.953 in |
| Height | 1.953 in |
| Length | 0.485 in |
| Trade Size | 1-1/4 in |
| Weight | 0.021 lb |
| Width | 1.953 in |

Certifications And Compliance

| | |
|----------------------|-----------|
| Certified Listed | UL Listed |
| Industry Standard(s) | UL 514B |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |
| Pallet Quantity | 12000 |

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195973-1](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - Conduit](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1405-SPEC-EN | REV 6/2024