



1-1/2 in. Rigid/IMC Bushing, Insulated

By RACO
Catalog # 1406

1-1/2 in. Rigid/IMC Bushing, Insulated



Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

Specifications

Buy American Compliant	No
Certified Listed	UL Listed
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 514B

Dimensions

Length	0.485 in
Trade Size	1-1/2 in
Weight	0.024 lb.
Height	2.188 in

Width	2.188 in
Dimensions	0.485 in x 2.188 in x 2.188 in

General

Conduit Type	Rigid/IMC
Insulation Type	Insulated
Fitting Type	Bushings
UPC	050169014066
Material	Polypropylene

Logistics

Minimum Pack Quantity	25
Pallet Quantity	12000
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)