



## 2 in. Rigid/IMC Bushing, Insulated

By Raco  
Catalog # 1408

2 in. Rigid/IMC Bushing, Insulated

### Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

### General

Catalog Number	1408
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Polypropylene
UPC	050169014080

### Dimensions

Dimensions	0.54 in x 2.64 in x 2.64 in
Height	2.64 in
Length	0.54 in
Trade Size	2 in
Weight	0.039 lb



\*Representative Image

Width 2.64 in

### Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
Certified Listed	UL Listed
Industry Standard(s)	UL 514B

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	7000

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC - E195973-1](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Specifications - 1408](#)  
[Terms and Conditions - HCC Terms & Conditions](#)