



# 2-1/2 in. Rigid/IMC Bushing, Insulated

By Raco  
Catalog # 1410

2-1/2 in. Rigid/IMC Bushing, Insulated



\*Representative Image

## Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

## General

Catalog Number	1410
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Polypropylene
UPC	050169014103

## Dimensions

Dimensions	0.63 in x 3.25 in x 3.25 in
Height	3.25 in
Length	0.63 in
Trade Size	2-1/2 in
Weight	0.06 lb
Width	3.25 in

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• TAA Compliant (All status valid till December 2024)</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	4800

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Certifications - UL COC - E195973-1](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Product Logo - Conduit](#)  
[SDS - HCC SDS](#)  
[Specifications - 1410](#)  
[Terms and Conditions - HCC Terms & Conditions](#)