



3 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # [1412](#)

3 in. Rigid/IMC Bushing, Insulated



*Representative Image

Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

General

Catalog Number	1412
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Polypropylene
UPC	050169014127

Dimensions

Dimensions	0.68 in x 3.9 in x 3.9 in
Height	3.9 in
Length	0.68 in
Trade Size	3 in
Weight	0.083 lb
Width	3.9 in

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• TAA Compliant (All status valid till December 2024)
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	2800

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Commercial Fittings](#)
[Certifications - UL COC - E195973-1](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Specifications - 1412](#)
[Terms and Conditions - HCC Terms & Conditions](#)