



3-1/2 in. Rigid/IMC Bushing, Insulated

By Raco
Catalog # 1414

3-1/2 in. Rigid/IMC Bushing, Insulated



*Representative Image

Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

General

Catalog Number	1414
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Polypropylene
UPC	050169014141

Dimensions

Dimensions	0.68 in x 4.41 in x 4.41 in
Height	4.41 in
Length	0.68 in
Trade Size	3-1/2 in
Weight	0.112 lb
Width	4.41 in

Certifications And Compliance

Certified Listed	UL Listed
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1980

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195973-1](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - Conduit](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand