



3-1/2 in. Universal Conduit Split Insulating Bushing

By Raco
Catalog # 1414USP



3-1/2 in. Universal Conduit Split Insulating Bushing

*Representative Image

Features

- Code-saver
- Innovative locking mechanism and hinge
- One-piece design: no need to fumble with extra pieces
- Easy, quick installation
- Low profile design
- No more damaged bushings during wire pulling
- Rated to 105° C

General

Application	Don't sweat it, just split it! RACO's Universal Split Bushing can be installed after wires and cables are pulled. Install on fittings, threaded or unthreaded Rigid/IMC, or EMT conduit. The innovative design lends a quick and easy installation, especially where space is limited.
Material	Polypropylene
UPC	050169814147

Dimensions

Dimensions	1.063 in x 4.25 in x 4.125 in
Height	4.125 in
Length	1.063 in
Trade Size	3.5 in
Weight	0.045 lb
Width	4.25 in

Certifications And Compliance

Certified Listed	cULus Listed
------------------	--------------

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	3500

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[SDS - HCC SDS](#)
[Sell Sheets - Universal Split Insulating Bushings](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1414USP-SPEC-EN | REV 6/2024