



# 6 in. Rigid/IMC Bushing, Insulated

By Raco  
Catalog # 1424

6 in. Rigid/IMC Bushing, Insulated

## Features

- Insuliner rated for 105° C
- Raised outside edges allow easy tightening by hand or tool
- UL Listed
- Available in trade sizes of 1/2 in. through 6 in.

## General

Catalog Number	1424
Conduit Type	Rigid/IMC
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Bushings
Insulation Type	Insulated
Material	Polypropylene
UPC	050169014240

## Dimensions

Dimensions	0.77 in x 7.06 in x 7.06 in
Height	7.06 in
Length	0.77 in
Trade Size	6 in
Weight	0.41 lb



\*Representative Image

Width	7.06 in
-------	---------

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	500

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195973-1](#)
- [Customer Notices - Prop65\\_Cancer](#)
- [Product Logo - Conduit](#)
- [SDS - HCC SDS](#)
- [Specifications - 1424](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand