



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps, Plaster Ears

By Raco
Catalog # 150



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps, Plaster Ears

Features

- Drawn steel construction with nonmetallic sheathed cable (NMSC)
- 4 in. x 1-1/2 in. deep
- Includes plaster ears for "cut-in" or "old work" applications
- Supplied with three 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

General

Bracket Type	No Bracket
Catalog Number	150
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169001509
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Dimensions	2 in x 4.75 in x 3.64 in
Fixture Lbs.	50 lb
Height	3.64 in
Length	2 in
Raised Ground	No
Weight	0.594 lb
Width	4.75 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	24
Packaging Type	No Packaging
Pallet Quantity	1920

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E3 - Exothermic Grounding](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978- 7](#)
[Sales Drawings - 150](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-150-SPEC-EN | REV 6/2024