



2-1/2 in. Rigid/IMC 3-Piece Super Coupling

By Raco
Catalog # 1530RAC



*Representative Image

2-1/2 in. Rigid/IMC 3-Piece Super Coupling

Features

- RACO three-piece couplings provide concrete-tight connections
- All components are zinc electro plated for corrosion protection
- Reduces installation time
- Eliminates field threading
- Lighter than the traditional malleable iron 3-piece coupling
- Compact size makes installation easier where space is limited
- No need to disassemble the compression nut and ring

General

Application	For use when coupling Rigid/IMC conduit to either threaded or unthreaded Rigid/IMC conduit, or EMT conduit Use couplings to couple conduit ends when the conduit cannot be turned
Catalog Number	1530RAC
UPC	050169015308

Dimensions

Dimensions	3.1 in x 3.45 in x 3.45 in
Height	3.45 in
Length	3.1 in
Trade Size	2.5 in
Weight	1.6 lb
Width	3.45 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	2
Minimum Pack Quantity	2
Pallet Quantity	700

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Sales Drawings - 1530RAC Customer Drawing](#)
[SDS - HCC SDS](#)
[Sell Sheets - 3 Piece Super Coupling](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-1530RAC-SPEC-EN | REV 6/2024