



3 in. Rigid/IMC 3-Piece Super Coupling

By Raco
Catalog # [1532RAC](#)



*Representative Image

3 in. Rigid/IMC 3-Piece Super Coupling

Features

- RACO three-piece couplings provide concrete-tight connections
- All components are zinc electro plated for corrosion protection
- Reduces installation time
- Eliminates field threading
- Lighter than the traditional malleable iron 3-piece coupling
- Compact size makes installation easier where space is limited
- No need to disassemble the compression nut and ring

Application

- For use when coupling Rigid/IMC conduit to either threaded or unthreaded Rigid/IMC conduit, or EMT conduit
- Use couplings to couple conduit ends when the conduit cannot be turned

General

Catalog Number 1532RAC
UPC 050169015322

Dimensions

Dimensions	3.33 in x 4.1 in x 4.1 in
Height	4.1 in
Length	3.33 in
Trade Size	3 in
Weight	2.028 lb
Width	4.1 in

Certifications And Compliance

Certified Listed UL Listed

Logistics

Carton Quantity 1
Pallet Quantity 567

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Sales Drawings - 1532RAC](#)
[SDS - HCC_SDS](#)
[Sell Sheets - 3 Piece Super Coupling](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1532RAC-SPEC-EN | REV 6/2024