



## 4 in. Rigid/IMC 3-Piece Coupling

By Raco  
Catalog # [1536RAC](#)

4 in. Rigid/IMC 3-Piece Coupling



\*Representative Image

### Features

- RACO three-piece couplings provide concrete-tight connections
- All components are zinc electro plated for corrosion protection
- Reduces installation time
- Eliminates field threading
- Lighter than the traditional malleable iron 3-piece coupling
- Compact size makes installation easier where space is limited
- No need to disassemble the compression nut and ring

### Application

- For use when coupling Rigid/IMC conduit to either threaded or unthreaded Rigid/IMC conduit, or EMT conduit
- Use couplings to couple conduit ends when the conduit cannot be turned

### General

UPC 050169015360

### Dimensions

Dimensions	3.56 in x 5.1 in x 5.1 in
Height	5.1 in
Length	3.56 in
Trade Size	4 in
Weight	2.87 lb
Width	5.1 in

### Certifications And Compliance

Certified Listed UL Listed

### Logistics

Carton Quantity	1
Pallet Quantity	336

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Sales Drawings - 1536RAC](#)  
[SDS - HCC\\_SDS](#)  
[Sell Sheets - 3 Piece Super Coupling](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
RACO-1536RAC-SPEC-EN | REV 6/2024