



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's & AC/MC/Flex Clamps, TS Bracket

By Raco
Catalog # 155



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's & AC/MC/Flex Clamps, TS Bracket

Features

- Drawn steel construction with "TS" side-mount bracket
- 4 in. x 1-1/2 in. deep
- BX clamps provided for steel and alum armored cable, MCI cable, MCI-A cable, and flexible conduit
- Supplied with two 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Catalog Number	155
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169001554
Wiring System	Armored Cable/Metal Clad/MCI-A/Flex

Dimensions

Actual Depth	2.04 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in

Fixture Lbs.	50 lb
Height	7 in
Raised Ground	No
Weight	0.656 lb
Width	4 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certified Listed	UL Listed

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1650

Product Assets

- [360 Product View - RACO_155](#)
- [3D Product View - RACO_155](#)
- [Catalogs - Steel Boxes, Covers and Accessories](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Sales Drawings - 155 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 155](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand