



## 4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Nine 1/2 in. KO's, J Bracket

By Raco  
Catalog # 158



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Nine 1/2 in. KO's, J Bracket

### Features

- Drawn steel construction with "J" bracket with spurs, slotted holes for toe-nailing, gauging notches at 3/8 in. and 1/2 in.
- 4 in. x 1-1/2 in. deep
- Supplied with nine 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

### General

Bracket Type	J, for Wood Studs
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169001585
Wiring System	Conduit

### Dimensions

Actual Depth	3.33 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	3.56 in
Raised Ground	No
Weight	0.612 lb
Width	4.11 in

### Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

### Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

### Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1800

### Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Certifications - UL COC - E195978-18](#)  
[Certifications - LEED Statement](#)  
[Certifications - NEMA OS1](#)  
[Sales Drawings - 158](#)  
[Sales Drawings - RACO-drawn-steel-box-infographic](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
RACO-158-SPEC-EN | REV 6/2024