



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Nine 1/2 in. KO's, J Bracket

By RACO
Catalog # [158](#)

4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Nine 1/2 in. KO's, J Bracket

Features

- Drawn steel construction with "J" bracket with spurs, slotted holes for toe-nailing, gauging notches at 3/8 in. and 1/2 in.
- 4 in. x 1-1/2 in. deep
- Supplied with nine 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

Specifications

Certified Listed	UL Listed
Buy American Compliant	Yes
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2026)

Configuration

Knockouts	1/2 in
Bracket Type	J, for Wood Studs

Current

Power Distribution Features	Fire Rated
-----------------------------	------------

Dimensions

Cubic Capacity	15.5 cu.in
Fixture Lbs.	50 lb.

Depth	1.5 in
Size	4 in
Actual Depth	3.33 in
Raised Ground	No
Width	4.11 in
Weight	0.612 lb.
Height	3.56 in

General

Wiring System	Conduit
Ceiling Fan Rated	No
Color	Gray
Type	Box
Material	Steel
Drawn or Welded	Drawn
UPC	050169001585

Logistics

Packaging Type	No Packaging
Carton Quantity	25
Pallet Quantity	1800

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)