



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps, J Bracket

By RACO
Catalog # 160



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Three 1/2 in. KO's & NMSC Clamps, J Bracket

Features

- Drawn steel construction with "J" bracket with spurs, slotted holes for toe-nailing and gauging notches at 3/8 in and 1/2 in. and nonmetallic sheathed cable clamps
- 4 in. x 1-1/2 in. deep
- Supplied with three 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

Specifications

Certified Listed	UL Listed
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Contact Manufacturer

Configuration

Knockouts	1/2 in
Bracket Type	J, for Wood Studs

Current

Power Distribution Features	Fire Rated
-----------------------------	------------

Dimensions

Cubic Capacity	15.5 cu.in
Fixture Lbs.	50 lb.
Depth	1.5 in
Length	3.33 in

Size	4 in
Actual Depth	3.33 in
Raised Ground	No
Width	4.067 in
Weight	0.655 lb.
Height	3.579 in
Dimensions	3.33 in x 4.067 in x 3.579 in

General

Wiring System	Nonmetallic Sheathed Cable
Ceiling Fan Rated	No
Color	Gray
Type	Box
Material	Steel
Drawn or Welded	Drawn
UPC	050169001608

Logistics

Packaging Type	No Packaging
Carton Quantity	25
Pallet Quantity	2000

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)