



4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's & NMSC Clamps, TS Bracket

By Raco
Catalog # 164

4 in. Octagon Box, Drawn, 1-1/2 in. Deep, Two 1/2 in. KO's & NMSC Clamps, TS Bracket



Features

- Drawn steel construction with "TS" side-mount bracket and L clamps for nonmetallic sheathed cable (NMSC)
- 4 in. x 1-1/2 in. deep
- Supplied with two 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 15.5 cu. in. capacity

General

Bracket Setback	0.5
Bracket Type	TS, for Metal or Wood Studs
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169001646
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.04 in
Cubic Capacity	15.5 cu.in
Depth	1.5 in
Fixture Lbs.	50 lb
Height	7 in
Raised Ground	No
Weight	0.642 lb
Width	4 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1750

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-164-SPEC-EN | REV 6/2024