



4 in. Octagon Box, Drawn, 2-1/8 in. Deep, Three 1/2 in. KO's & NMSC Clamps

By Raco
Catalog # 175



4 in. Octagon Box, Drawn, 2-1/8 in. Deep, Three 1/2 in. KO's & NMSC Clamps

Features

- Drawn steel construction
- 4 in. x 2-1/8 in. deep
- L clamps provided for non-metallic sheathed cable (NMSC)
- Supplied with three 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 21.5 cu. in. capacity

General

Bracket Type	No Bracket
Catalog Number	175
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Size	4 in
Type	Box
UPC	050169001752
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	2.188 in
Cubic Capacity	21.5 cu.in
Depth	2.125 in
Fixture Lbs.	50 lb
Height	4 in
Raised Ground	No
Weight	0.693 lb
Width	4 in

Electrical Ratings

Power Distribution Features	Fire Rated
-----------------------------	------------

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	2000

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-18](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-175-SPEC-EN | REV 6/2024