



4 in. Octagon Box, Drawn, 2-1/8 in. Deep, Two 1/2 in. KO's & NMSC Clamps, TS Bracket

By Raco
Catalog # 176



4 in. Octagon Box, Drawn, 2-1/8 in. Deep, Two 1/2 in. KO's & NMSC Clamps, TS Bracket

Features

- Drawn steel construction with "J" bracket with spurs, slotted holes for toe-nailing and gauging notches at 3/8 in and 1/2 in. and nonmetallic sheathed cable clamps
- 4 in. x 2-1/8 in. deep
- Supplied with three 1/2 in. knockouts
- Combination Phillips/slotted screw heads
- 21.5 cu. in. capacity

General

Bracket Setback	0.625
Bracket Type	J, for Wood Studs
Ceiling Fan Rated	No
Color	Gray
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Knockouts	1/2 in
Material	Steel
Number of Gang(s)	1-Gang
Size	4 in
Type	Box
UPC	050169001769
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Actual Depth	3.125 in
Cubic Capacity	21.5 cu.in
Depth	2.125 in
Fixture Lbs.	50 lb
Height	3.625 in
Raised Ground	No
Weight	0.818 lb
Width	4.375 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	25
Packaging Type	No Packaging
Pallet Quantity	1625

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-21](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-176-SPEC-EN | REV 6/2024