



## 3/4 in. Rigid/IMC Compression Connector, Uninsulated

By RACO  
Catalog # 1803

3/4 in. Rigid/IMC Compression Connector, Uninsulated



### Features

- All steel/malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes 1/2 in. through 4 in.

### Specifications

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
EU RoHS Indicator	Yes
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL 514B

### Configuration

Connector Type	Compression
----------------	-------------

### Dimensions

Length	1.5 in
--------	--------

Trade Size	3/4 in
Weight	0.181 lb.
Height	1.297 in
Width	1.297 in
Dimensions	1.5 in x 1.297 in x 1.297 in

### General

Conduit Type	Rigid/IMC
Fitting Type	Connectors
UPC	050169018033
Material	Steel/Malleable Iron

### Logistics

Minimum Pack Quantity	25
Pallet Quantity	8000
Carton Quantity	25

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)