



1-1/4 in. Rigid/IMC Compression Connector

By Raco
Catalog # 1805



1-1/4 in. Rigid/IMC Compression Connector, Uninsulated

Features

- All steel/malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes 1/2 in. through 4 in.

General

Catalog Number	1805
Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Yes
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169018057

Dimensions

Dimensions	1.938 in x 1.953 in x 1.953 in
Height	1.953 in
Length	1.938 in

Trade Size	1-1/4 in
Weight	0.524 lb
Width	1.953 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1600

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195969- 1](#)
[Product Logo - Conduit](#)
[Sales Drawings - 1805 Customer Drawing](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)