



2-1/2 in. Rigid/IMC Compression Connector

By Raco
Catalog # 1810



*Representative Image

2-1/2 in. Rigid/IMC Compression Connector, Uninsulated

Features

- Malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes 1/2 in. through 4 in.

General

Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169018101

Dimensions

Dimensions	4 in x 4.141 in x 4.141 in
Height	4.141 in
Length	4 in
Trade Size	2-1/2 in
Weight	1.848 lb
Width	4.141 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	560

Product Assets

[Brochures - HCC Products for Solar](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop65_Cancer](#)
[Product Logo - Conduit](#)
[Sales Drawings - 1810](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-1810-SPEC-EN | REV 6/2024