



# 3-1/2 in. Rigid/IMC Compression Connector

By Raco  
Catalog # 1814



3-1/2 in. Rigid/IMC Compression Connector, Uninsulated

## Features

- 
- 
- 
- 
- 
- 

## General

Catalog Number	1814
Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169018149

## Dimensions

Dimensions	4.375 in x 5.375 in x 5.375 in
Height	5.375 in
Length	4.375 in
Trade Size	3-1/2 in

Weight	3.15 lb
Width	5.375 in

## Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	336

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Customer Notices - Prop65\\_Cancer](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 1814 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 1814](#)
- [Terms and Conditions - HCC Terms & Conditions](#)