



# 4 in. Rigid/IMC Compression Connector, Uninsulated

By Raco  
Catalog # 1816



4 in. Rigid/IMC Compression Connector, Uninsulated

## Features

- Malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Noninsulated
- Hex compression nuts assure easy wrench installation
- UL Listed, CSA
- Available in trade sizes 1/2 in. through 4 in.

## General

Catalog Number	1816
Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Contact Manufacturer
Fitting Type	Connectors
Material	Steel/Malleable Iron
UPC	050169018163

## Dimensions

Dimensions	4.5 in x 5.906 in x 5.906 in
Height	5.906 in
Length	4.5 in
Trade Size	4 in

Weight	4.45 lb
Width	5.906 in

## Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none"><li>• UL Listed</li><li>• CSA Certified</li></ul>
Industry Standard(s)	UL 514B

## Logistics

Carton Quantity	1
Minimum Pack Quantity	1
Pallet Quantity	336

## Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)  
[Catalogs - Commercial Fittings](#)  
[Customer Notices - Prop65\\_Cancer](#)  
[Product Logo - Conduit](#)  
[Sales Drawings - 1816 Customer Drawing](#)  
[SDS - HCC SDS](#)  
[Specifications - 1816](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand