



1-1/4 in. Rigid/IMC Compression Coupling

By Raco
Catalog # 1825

1-1/4 in. Rigid/IMC Compression Coupling

Features

- All steel/malleable iron construction ensures mechanical protection for the raceway
- Zinc-electroplated for added corrosion protection
- Hex compression nuts assure easy wrench installation
- Available in trade sizes 1/2 in. through 4 in.

General

Catalog Number	1825
Conduit Type	Rigid/IMC
Connector Type	Compression
EU RoHS Indicator	Yes
Fitting Type	Couplings
Material	Steel/Malleable Iron
UPC	050169018255

Dimensions

Dimensions	1.938 in x 1.953 in x 1.953 in
Height	1.953 in
Length	1.938 in
Trade Size	1-1/4 in
Weight	0.849 lb



Width	1.953 in
-------	----------

Certifications And Compliance

Buy America(n) Qualified Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514B

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	1330

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Commercial Fittings](#)
- [Certifications - UL COC - E195969-1](#)
- [Product Logo - Conduit](#)
- [Sales Drawings - 1825 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Specifications - 1825](#)
- [Terms and Conditions - HCC Terms & Conditions](#)