



4 in. Square Box, Drawn, 1-1/4 in. Deep with Fifteen 1/2 in. KO's

By RACO
Catalog # 185

4 in. Square Box, Drawn, 1-1/4 in. Deep with Fifteen 1/2 in. KO's



Features

- Ideal for exposed work applications
- Combination screw heads allow quick installation
- Drawn construction
- Fifteen 1/2 in. knockouts
- UL Listed
- 18.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls
- UPC barcoded

Specifications

Certified Listed	UL Listed
Buy American Compliant	Yes
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2026)

Configuration

Knockouts	1/2 in
Bracket Type	No Bracket
Number of Gang(s)	2-Gang

Dimensions

Cubic Capacity	18.0 cu.in
Depth	1.25 in

Size	4 in
Actual Depth	1.313 in
Raised Ground	No
Width	4 in
Weight	0.593 lb.
Height	4 in

General

Wiring System	Conduit
Color	Gray
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Drawn
UPC	050169001851

Logistics

Packaging Type	No Packaging
Standard Package	50
Carton Quantity	50
Pallet Quantity	3000

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)