



## 4 in. Square Box, Welded, 1-1/2 in. Deep with Ten 1/2 in. KO and Six TKO's, Raised Ground

By RACO  
Catalog # 189

4 in. Square Box, Welded, 1-1/2 in. Deep with Ten 1/2 in. KO and Six TKO's, Raised Ground



### Features

- TKO knockout design provides installation flexibility
- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 in. knockouts and six TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Raised ground
- Acceptable in 2-hour fire rated walls

### Specifications

Certified Listed	UL Listed
Buy American Compliant	Yes
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2026)

### Configuration

Knockouts	<ul style="list-style-type: none"> <li>• 1/2 in</li> <li>• 1/2 - 3/4 in Combination (TKO)</li> </ul>
Bracket Type	No Bracket

### Dimensions

Cubic Capacity	21.0 cu.in
----------------	------------

Depth	1.5 in
Size	4 in
Actual Depth	1.563 in
Raised Ground	Yes
Width	4 in
Weight	0.703 lb.
Height	4 in

### General

Wiring System	Conduit
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Welded
UPC	050169901892

### Logistics

Packaging Type	No Packaging
Carton Quantity	50
Pallet Quantity	2750

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)