



4 in. Square Box, Welded, 1-1/2 in. Deep with Ten 1/2 in. KO and Six TKO's, Raised Ground

By Raco
Catalog # 189



4 in. Square Box, Welded, 1-1/2 in. Deep with Ten 1/2 in. KO and Six TKO's, Raised Ground

Features

- TKO knockout design provides installation flexibility
- Combination screw heads allow quick installation
- Welded construction
- Ten 1/2 in. knockouts and six TKO knockouts
- UL Listed
- 21.0 cu. in. capacity
- Raised ground
- Acceptable in 2-hour fire rated walls

General

Bracket Type	No Bracket
Drawn or Welded	Welded
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in;1/2 - 3/4 in Combination (TKO)
Material	Steel
Type	Box
UPC	050169901892
Wiring System	Conduit

Dimensions

Actual Depth	1.563 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	4 in
Raised Ground	Yes
Weight	0.703 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2750

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - UL COC - E195978-1](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Sales Drawings - 189](#)
[Sales Drawings - RACO-welded-steel-box-infographic](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
RACO-189-SPEC-EN | REV 6/2024