



4 in. Square Box, Drawn, 1-1/2 in. Deep with Sixteen 1/2 in. KO's, Raised Ground

By RACO
Catalog # 190

4 in. Square Box, Drawn, 1-1/2 in. Deep with Sixteen 1/2 in. KO's, Raised Ground



Features

- Ideal for exposed work applications
- Combination screw heads allow quick installation
- Drawn construction
- Sixteen 1/2 in. knockouts
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls

Specifications

Certified Listed	UL Listed
Buy American Compliant	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	Buy American Act Compliant (All status valid till December 2026)

Configuration

Knockouts	1/2 in
Bracket Type	No Bracket

Dimensions

Cubic Capacity	21.0 cu.in
Depth	1.5 in

Size	4 in
Actual Depth	1.563 in
Raised Ground	Yes
Width	4 in
Weight	0.66 lb.
Height	4 in

General

Wiring System	Conduit
Type	Box
Fire Resistance	Yes
Material	Steel
Drawn or Welded	Drawn
UPC	050169901908

Logistics

Packaging Type	No Packaging
Carton Quantity	50
Pallet Quantity	2750

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)