



4 in. Square Box, Drawn, 1-1/2 in. Deep with one 1/2 in. and eleven 3/4 in. KO's, Raised Ground

By Raco
Catalog # 191



4 in. Square Box, Drawn, 1-1/2 in. Deep with one 1/2 in. and eleven 3/4 in. KO's, Raised Ground

Features

- Ideal for exposed work applications
- Combination screw heads allow quick installation
- Drawn construction
- Eleven 3/4 in. knockouts and one 1/2 in. knockout
- UL Listed
- 21.0 cu. in. capacity
- Acceptable in 2-hour fire rated walls

General

Bracket Type	No Bracket
Drawn or Welded	Drawn
EU RoHS Indicator	Contact Manufacturer
Fire Resistance	Yes
Knockouts	1/2 in.;3/4 in
Material	Steel
Type	Box
UPC	050169901915
Wiring System	Conduit

Dimensions

Actual Depth	1.563 in
Cubic Capacity	21 cu.in
Depth	1.5 in
Height	4 in
Raised Ground	Yes
Weight	0.665 lb
Width	4 in

Certifications And Compliance

Certified Listed	UL Listed
------------------	-----------

Logistics

Carton Quantity	50
Packaging Type	No Packaging
Pallet Quantity	2750

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Certifications - LEED Statement](#)
[Certifications - NEMA OS1](#)
[Certifications - UL COC - E195978-5](#)
[Sales Drawings - RACO-drawn-steel-box-infographic](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
RACO-191-SPEC-EN | REV 6/2024